

Agilent Vacuum Product Declarations of Conformity reference list - 26.11.25

Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
Leak Detector	C15	G8603-90002	Rev E.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033, 2014/53/UE (RED) - S.I. 2017 N° 1206	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 301489-1 (2017)
	VS	G8603-90002	Rev E.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033, 2014/53/UE (RED) - S.I. 2017 N° 1206	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 301489-1 (2017)
	HLD	G8603-90002	Rev E.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033, 2014/53/UE (RED) - S.I. 2017 N° 1206	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 301489-1 (2017)
	HLD +Wi-Fi	G8603-90002	Rev E.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033, 2014/53/UE (RED) - S.I. 2017 N° 1206	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 301489-1 (2017)
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
Scroll Pumps	TS*** (non-inverters)	X3814-90001	Rev E.00	23.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN 63000 (2018), EN 60034-30 (2015)*
	TS*** (non-inverters) NO TAMPER PROOF (applicable only to 20001660 (Inficon), X3814-64201, X3828-64201)	X3828-90001	Rev A.00	25.09.25	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN 63000 (2018)
	TS*** (Inverters)	X3806-90000	Rev F.00	23.09.25	2006/42/EC (MD), 2014/30/UE (EMC), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 60034-30 (2015)*
	IDP-3	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*
	IDP-7	X3806-90000	Rev F.00	23.09.25	2006/42/EC (MD), 2014/30/UE (EMC), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 60034-30 (2015)*
	IDP-10	X3806-90000	Rev F.00	23.09.25	2006/42/EC (MD), 2014/30/UE (EMC), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 60034-30 (2015)*
	IDP-15	X3806-90000	Rev F.00	23.09.25	2006/42/EC (MD), 2014/30/UE (EMC), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018), EN 60034-30 (2015)*
	IDP-35 & IDP-45	X3835-90012	Rev. A.00	08.10.24	2006/42/EC (MD), 2014/30/UE (EMC), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (1996) A1 (2009), EN12100 (2010), EN 61010-1 (2010) / A1 (2019), EN 61326-1 (2013), EN 55011 (2016), A1 (2017) A2 (2021) (Class A), EN 61000-3-2 (2019), EN 61000-3-3 (2013) A1 (2019), EN 61000-6-2 (2019), EN 63000 (2018), EN 60034-30 (2015), IEC 61010 1 (2010)/A1 (2016), UL 61010-1 (3RD EDITION), CAN/CSA C22.2 No 61010-1-12, IEC 61326-1 (2012), ICES/NMB-001:2014, KN 61000-2 (2017), KN 61000-4-2, KN 61000-4-8, KN 61000-4-3
	IDP-4	X3802-90000	Rev. A.00	24.11.25	2006/42/EC (MD), 2014/30/UE (EMC), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2021), 63000 (2018), EN 60034-30 (2015)*
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
Vacuum Gauge Contr.	AGC-100	X3000-90001	Rev C.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	AGD-100	X3000-90001	Rev C.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	RGC-100	X3000-90001	Rev C.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)

* When is applicable

* When is applicable

* When is applicable

* When is applicable

* When is applicable

* When is applicable

* When is applicable

	RGC-150	X3000-90001	Rev C.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
XGS-600	XGS-600	X3000-90003	Rev C.00	27.10.21	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 61326-1 (2013), EN 63000 (2018)
Inverted magnetron Pirani Gauge	FRG700 - FRG702 CDG 500	X3000-90001	Rev C.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
Turbo controllers	Rack AG (74, 84, 301, 304, 305)	86.100121	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	Rack Medium (551, 701, 704, 1001, 2300, 1kG)	86.100121	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	On board Controller 70, 81, 84, 301, 304, 305, 551, 701, 704, 1001, 1kG)	86.100121	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	PCB Controller (70, 81,301, 304)	86.100123 (*)	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
(*) Declaration of Incorporation						
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
TMP Without inverter (1/2)	70	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	74	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	84	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	301	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	301 SF	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	301 SSF	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	304	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	305 FS	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	305 FSQ	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
TMP Without inverter (2/2)	401	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	404	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	551	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	701	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	704	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	804	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	1001	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)

	1K-G	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	2300	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
TMP with Inverter	305-IC	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	305-ICQ	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	2K-G	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
Pumping Systems	IPS	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	TPS Mini	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	TPS Compact	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	TPS Mobile	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
Ion Pumps	Ion pump every family without heater	86.100125	Rev F.00	27.10.21	2006/42/EC (MD) - S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN 63000 (2018)
	TSP cartridge	86.100125	Rev F.00	27.10.21	2006/42/EC (MD) - S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN 63000 (2018)
	Ion pump every family with heater	86.100122	Rev G.00	10.05.22	2006/42/EC (MD) S.I. 2008 N° 1597, 2011/65/UE modified by EU 2015/863 (RoHS), S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
Ion Controllers	IPC Mini	86.100121	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	IPCU	86.100121	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	4UHV	86.100121	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
	TSP	86.100121	Rev G.00	10.05.22	2014/30/UE (EMC) - S.I. 2016 N° 1091, 2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)
Accessories	Heater	86.100124	Rev G.00	10.05.22	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
	Solenoid/Electromagnetic Valve	86.100124	Rev G.00	10.05.22	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN61010-1 (2010)/A1 (2019), EN 63000 (2018)
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards
Rotary Vane Pumps	DS40M	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*
	DS102	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*

* When is applicable

* When is applicable

	DS202	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*	* When is applicable
	DS302	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*	* When is applicable
	DS402	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*	* When is applicable
	DS602	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*	* When is applicable
	HS602	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*	* When is applicable
	HS652	X3803-90000	Rev F.00	25.09.25	2006/42/EC (MD), 2011/65/UE modified by EU 2015/863 (RoHS), 2019-1781 EU (Ecodesign Regulation)	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 63000 (2018), EN 60034-30 (2015)*	* When is applicable
RVP Single Stage	MS40	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)	
	MS120	86.100120	Rev G.00	10.05.22	2006/42/EC (MD) - S.I. 2008 N° 1597, 2014/30/UE (EMC) - S.I. 2016 N° 1091, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 1012-2 (2009), EN 12100 (2010), EN61010-1 (2010)/A1 (2019), EN 61326-1 (2013), EN 63000 (2018)	
Product	Sub-family	CE Doc Part Number	CE Doc Rev	Date	EU Directives / Regulation	Standards	
Diffusion Pumps	NH-35	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	HS-32	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	HS-20	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	HS-16	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	HS-2	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	VHS-400	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	VHS-250	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	VHS-10	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	VHS-6	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	VHS-4	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	
	AX-65	X3900-90000	Rev E.00	27.10.21	2014/35/UE (LVD) - S.I. 2016 N° 1101, 2011/65/UE modified by EU 2015/863 (RoHS) - S.I. 2012 N° 3032, 3033	EN 63000 (2018)	